

ALSTACOL 25+

Alcohol based Surface Disinfectant

General Description

ALSTACOL 25+ is a ready to use blend of alcohol, quaternary compound and cleaning agents that can effectively disinfect doorknobs, handles, mobile phones, car steering wheels, keyboards, and all hard contact surfaces and equipment, in regular human contact manifesting broad spectrum bactericidal, fungicidal and virucidal attribute.

The coactive operation of Quaternary compound in the presence of alcohol breaks down the lipoprotein complexes inside the microorganisms' cell, opening its membrane which allows the alcohol to pierce and rupture its total structure. ALSTACOL 25+ is competent to be used at In-house, Commercial and Industrial application surfaces.

Key Features & Benefits

- Alcohol based Ready-To-Use product
- Rapid action, spray and wipe
- Highly effective in removing most infection spreading germs
- Non-tainting, non-staining nature, does not alter the property of application system, be it metal, non-metal, glass, etc.
- Enhanced sanitation performance
- Easy to dose & apply

Physicochemical Data

Attributes	UOM	Typical Value
Form	-	Clear liquid
Appearance	-	Slight Blue
Odour	-	Alcohol Type
Ethanol, 2-Propanol, 1-Propanol blend	% vol.	70.0 min.
Assay as Quaternary Ammonium Compounds	% vol.	0.3
Other Ingredients	-	Balance
Solubility	-	Soluble in water

Handling Measures

Proper safety products such as splash goggles, gloves, lab coat should be worn while handling and applying chemicals. Splashes on skin to be washed off with water immediately. In case of splashing into the eyes, flush them with fresh water and seek medical attention. *Should not be injected.*

Storage

Flammable Product! Store in cool, dry well ventilated area in tightly closed, plainly labelled containers. Keep away from incompatible materials. Containers, even when empty, will retain residue and vapours. Separate from acids, alkalis, reducing agents and combustibles.

Shelf life: 2 Years when stored properly.

Kindly refer label and SDS for details.

Packaging

ALSTACOL 25+ is available in 500ml trigger spray, 5L jars.



Dosage & Application

Aim at the target area, spray and wipe with a lint free cloth. For hard surfaces, the solution is allowed to remain for 5 seconds.

For more details on use concentration, kindly contact your nearest CSL Representatives.

Contact Information

Chemtex Speciality Limited

Haute Street Corporate Park 86A
Topsia Road (S), Kolkata, WB, India

Tel: +91-33-7111-1111
E:info@chemtexlimited.com

ISO 9001: 2015, ISO 14001: 2007 (EMS),
OHSAS 18001: 2015, WHO-GMP Certified,
and CRISIL SE-2B rated company

Disclaimer: The statements, technical information and recommendations contained herein are believed to be accurate as of the date hereof. Since the conditions and methods of use of the product and of the information referred to herein are beyond our control, Chemtex Speciality Limited expressly disclaims any and all liability as to any results obtained or arising from any use of the product or reliance on such information; NO WARRANTY OF FITNESS FOR ANY PARTICULAR PURPOSE, WARRANTY OF MERCHANTABILITY OR ANY OTHER WARRANTY, EXPRESSED OR IMPLIED, IS MADE CONCERNING THE GOODS DESCRIBED OR THE INFORMATION PROVIDED HEREIN.

2020 © Chemtex Speciality Limited